



- NOTES:
- TO COMPLY WITH ANSI Z358.1-2009 FOR EMERGENCY EYEWASH OR EYEFACE WASH:
    - UNIT SHALL BE INSTALLED IN ACCORDANCE WITH MANUFACTURER'S INSTRUCTIONS AND ACCEPTABLE PLUMBING PRACTICES.
    - EYEWASH OR EYEFACE WASH SHALL BE POSITIONED WITH NOZZLES NOT LESS THAN 33.8 CM (13.3 IN.) AND NO GREATER THAN 114.3 CM (45 IN.) FROM SURFACE ON WHICH USER STANDS AND 15.3 CM (6 IN.) MINIMUM FROM WALL OR NEAREST OBSTRUCTION.
  - DIMENSIONS MAY VARY BY  $\pm$  1/2 (13).

- USE SUPPLIED SCREWS TO INSTALL THE UNIT ON WALL STRUCTURE.
- FLOW RATE FOR EYEFACE WASH IS 5 GPM AND EXCEEDS ANSI Z358.1-2009 STANDARD.

**Haws Corporation**

1455 KLEPPE LANE  
SPARKS, NEVADA 89431  
(775) 359-4712 FAX (775) 359-7424  
E-MAIL: HAWS@HAWSCO.COM  
WEBSITE: WWW.HAWSCO.COM

EQUIP. NO.	TRANSFER NO.	MODEL(S)	DATE
7656WC	HR	7656WC EYEFACE WASH	08/20/13
DATE	CHKD.	LINEO FAX DOC #	2765682
APPROVER	DATE	SCALE	INSTALLATION/REWORK
0002080088 D	13727A00	7	