

FEATURES & BENEFITS

CONSTRUCTION

Heavy-duty vinyl construction provides durable, long-lasting protection against dust, dirt, and debris in harsh industrial and outdoor environments.

INSTALLATION

Easy installation with secure Velcro straps allows for quick attachment and removal without tools, saving time during setup and inspections.

CLEANING AND MAINTENANCE

Smooth, easy-to-clean surface helps maintain sanitary eyewash equipment, ensuring readiness and compliance with safety regulations.



OPTIONS

- 7501 - Portable Eyewash
- 9082 - Bacteriostatic Water Preservative
- 9083 - HAWSCLEAN™ Portable Eyewash Cleansing Stick

For more information, visit www.hawsco.com or call (888) 640-4297.

SPECIFICATIONS


The Haws 9128 Dust Cover is designed to safeguard the [Haws 7501 Portable Eyewash](#) (Not Included) from dust and airborne particulates, ensuring continued reliability in critical environments. Constructed from clear, durable vinyl, this cover allows for easy visual inspection while providing a secure protective barrier. Engineered for seamless installation and dependable performance, it helps maintain the integrity of your emergency eyewash station, ensuring it is always ready for use.

APPLICATIONS

Designed for use in dusty, dirty, or debris-prone environments, the Portable Eyewash Dust Cover helps protect eyewash nozzles and water reservoirs from contamination when not in use. Ideal for construction sites, industrial plants, outdoor facilities, and warehouses, this cover preserves the cleanliness and readiness of emergency eyewash stations, ensuring clean, reliable water is available in the event of an emergency. Easy to install and remove, it's a simple yet effective solution for maintaining compliance and operational safety in harsh or unpredictable conditions.

NOTES:

1. TO COMPLY WITH ANSI Z358.1-2014 FOR EMERGENCY EYEWASH AND SHOWER EQUIPMENT:
 - UNIT SHALL BE INSTALLED IN ACCORDANCE WITH MANUFACTURER'S INSTRUCTIONS AND ACCEPTABLE PLUMBING PRACTICES.
 - EYEWASH STREAMS SHALL BE POSITIONED SUCH THAT STREAMS ARE 15.3 CM (6 IN.) MINIMUM FROM THE WALL OR NEAREST OBSTRUCTION AND, WHEN FLOWING AT 30-30.5 PSI, MEET ANSI GAUGE REQUIREMENTS BETWEEN 83.8 & 134.6 CM (33-53 IN) ABOVE FLOOR.
2. AFTER INSTALLATION, CHECK EYEWASH FUNCTION TO ENSURE THAT THE UNIT IS STILL IN COMPLIANCE WITH THE REQUIREMENTS OF PERTINENT CODES AND STANDARDS (E.G., DIMENSIONS, ACTIVATION, FLOW CHARACTERISTICS, ETC.).




STEP 1

EMPTY THE 7501 PORTABLE EYEWASH IF IT IS NOT ALREADY EMPTY. PULL THE VINYL COVER OVER THE MODEL 7501 EYEWASH.

STEP 2

CLOSE THE BOTTOM PANEL OF THE VINYL COVER AND ATTACH THE VELCRO ON EITHER SIDE.



STEP 3

OPEN THE FRONT VELCRO FLAP BY PULLING THE YELLOW STRAP. PULL THE YELLOW EYEWASH ARM DOWN ON THE 7501 AND ATTACH THE BLACK NYLON WEBBING LOOP AROUND THE EYEWASH ARM BELOW THE EYEWASH HEADS.

STEP 4

MOUNT ASSEMBLED EYEWASH AND VINYL COVER IN ACCORDANCE WITH EYEWASH INSTALLATION INSTRUCTIONS.



1455 KLEPPE LANE
SPARKS, NEVADA 89431
(775) 359-4712 FAX (775) 359-7424
E-MAIL: HAWS@HAWS.CO.COM
WEBSITE: WWW.HAWS.CO.COM

ECN: 6209	REV. ECN: 6209	BY: JU	MODEL(S)	PART NUMBER
DRAWN: JU	DATE: 11/05/24	CHKD: JU	9128, 7501 CLEAR VINYL COVER	0510002290
APPROVED: JL	DATE: 03/12/25	SCALE: 1:8	DRAWING TYPE: INSTALLATION	REVISION 1
			SIZE: A	SHEET 1 OF 1